



Attachment eye Quick Lift DSR, Thread Ø: M24X3



Order data

Order number	086454 M24X3
GTIN	2050002053885
Item class	08Y

Description

Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

Note:

SF 5:1 = Safety Factor 5.

Technical description

Weight	2.6 kg
Thread Ø	M24x3
Eye width E	55 mm
Eye thickness F	25 mm

Internal hexagon size across flats S	40 mm
Lifting capacity WLL SF 5:1	2.5 t
Screw head \varnothing C	60 mm
Height of screw head A	55 mm
Distance from centre divider to eye D	83 mm
Attachment eye width G	115 mm
Height of centre divider B	55 mm
Thread length L	36 mm
Type of product	Attachment eye