



Attachment eye Quick Lift DSR, Thread \varnothing : M12X1,75



Order data

Order number	086454 M12X1,75
GTIN	2050002053847
Item class	08Y

Description

Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

Note:

SF 5:1 = Safety Factor 5.

Technical description

Internal hexagon size across flats S	27 mm
Height of centre divider B	40 mm
Screw head \varnothing C	45 mm
Eye thickness F	17 mm

Eye width E	38 mm
Lifting capacity WLL SF 5:1	0.65 t
Distance from centre divider to eye D	53 mm
Height of screw head A	40 mm
Weight	0.9 kg
Attachment eye width G	76 mm
Thread length L	23 mm
Thread Ø	M12×1.75
Type of product	Attachment eye