



## Attachment eye Quick Lift DSR, Thread $\varnothing$ : M16X2



### Order data

Order number	086454 M16X2
GTIN	2050002053861
Item class	08Y

### Description

#### Version:

Compact, high-strength steel Quick Lift DSR attachment eye for screwing in. Rotates 360°, pivots 180°. Time saving of up to 80% compared with screwing in a traditional attachment eye (DSR vs. Quick Lift DSR). **Can be rotated under load.** Easy to use as the system is purely mechanical. Maintenance-free, safe and reliable. The Quick Lift DSR can be fastened in the internal thread in seconds by pressing in the screw head. This is a purely mechanical process based on actuating a spring.

#### Note:

**SF 5:1 = Safety Factor 5.**

### Technical description

Eye width E	38 mm
Height of centre divider B	40 mm
Lifting capacity WLL SF 5:1	1.05 t
Thread $\varnothing$	M16x2

Internal hexagon size across flats S	27 mm
Eye thickness F	17 mm
Attachment eye width G	76 mm
Weight	0.9 kg
Screw head $\varnothing$ C	45 mm
Thread length L	27 mm
Distance from centre divider to eye D	53 mm
Height of screw head A	40 mm
Type of product	Attachment eye