

Flat magnet without thread, Ferrite, Ø: 25mm



Order data

Order number	085910 25
GTIN	2050000965050
Item class	08Q

Description

Version:

Shielded flat magnets with magnetic core made of **hard ferrite**.

- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by pressing in / gluing and fixing / holding.

Technical description

Height	7 mm
Nominal clamping force	40 N
Weight	19 g
maximum temperature resistance	120 °C
Ø	25 mm
Material of the magnet core	Ferrite
Type of product	Flat gripper magnet