



Reversible precision ratchet, 3/8 inch, Type: 3/8



Order data

Order number	635176 3/8
GTIN	4000896235063
Item class	630

Description

Version:

With reversing lever for right-hand and left-hand threads, working arc 4°.

Standard:

Außenvierkant nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkant nach **DIN 3120-C 10** mit Rillen.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for:

Manual use.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 635145

Technical description

Square drive	3/8 in
overall length	200 mm
No. of teeth	90
Working angle	4 degrees
Material	Chrome vanadium steel

Type of product

Ratchet