



## MultiMaster MM 500 Plus Top, Type: 72296761



### Order data

Order number	077814 72296761
GTIN	4014586893235
Item class	03F

### Description

#### Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Powerful MultiTool for rapid work progress (for interior work and renovation) with more than 30 accessories for sawing wood and metal, cutting tiles, and more.

#### Supplied with:

30-piece accessories set, 1× dust extractor, 1× plastic tool case.

30-piece accessories set consisting of: 1× E-Cut long-life saw blade (10 mm), 2× E-Cut long-life saw blades (35 mm), 2× E-Cut long-life saw blades (65 mm), 1× E-Cut Carbide Pro saw blades (32 mm), 1× carbide saw blade (Ø 75), 1× carbide rasp (three-square), 1× scraper, 1× perforated abrasive plate, 1× each perforated abrasive plate (K60, K80, K120, K180).

Packaging: Carrying case

Manufacturer's designation: MM 500 PLUS TOP

Power consumption: 350 W

Toolholder: Starlock, Starlock Plus

Speed of oscillation: 10000 min<sup>-1</sup>

Amplitude (oscillation movement):  $2 \times 1.7^\circ$

Weight: 1.4 kg

---

## Technical description

Manufacturer's designation	MM 500 PLUS TOP
Toolholder	Starlock, Starlock Plus
Power consumption	350 W
Weight	1.4 kg
Amplitude (oscillation movement)	$2 \times 1.7^\circ$
Speed of oscillation	$10000 \text{ min}^{-1}$
Packaging	Carrying case
Type of product	Oscillator