



## MultiMaster MM 700 Max, Type: 72296862



### Order data

Order number	077804 72296862
GTIN	
Item class	03F

### Description

#### Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

#### Supplied with:

1× E-Cut universal saw blade (44 mm), L-BOXX.

### Technical description

Power supply	Battery-powered
Power consumption	450 W

Weight	1.6 kg
Manufacturer's designation	MM 700 MAX
Speed of oscillation	10000 min <sup>-1</sup>
Toolholder	StarlockMax
Amplitude (oscillation movement)	2 × 2.0 °
Packaging	Modular case (L-Boxx)
Type of product	Oscillator

## Accessories

E-Cut saw blade, diamond Width of cut 44 mm	077885 44
E-Cut saw blade, carbide, SLP mount Width of cut 35 mm	077858 35
Segmented saw blade, diamond, 2.2 mm Saw blade Ø 90 mm	077867 90
E-Cut saw blade, curved Cutting width 50 mm	077870 50
Segmented saw blade, solid HSS Saw blade Ø 85 mm	077836 85
Segmented saw blade, carbide, 2.2 mm Saw blade Ø 75 mm	077865 75
E-Cut saw blade, Carbide Pro Cutting width 35 mm	077891 35
E-Cut saw blade, diamond, 2.2 mm	077886
E-Cut saw blade set, wood + metal 6 pieces Version SET	077848 SET
Saw blade, bi-metal HSS Saw blade Ø 100 mm	077838 100
Carbide rasp, 3-square	077888
Segmented saw blade, bi-metal HSS Saw blade Ø 100 mm	077827 100
Saw blade, solid HSS, 5 pieces Saw blade Ø 85 mm	077835 85
Saw blade, solid HSS Saw blade Ø 85 mm	077834 85
E-Cut saw blade, bi-metal, long-Life Width of cut 32 mm	077884 32
Segmented saw blade, carbide, 2.2 mm Saw blade Ø 90 mm	077865 90
Segmented saw blade, diamond Saw blade Ø 90 mm	077868 90

E-Cut saw blade, standard Cutting width 35 mm	077844 35
E-Cut saw blade, bi-metal, long-Life Width of cut 42 mm	077884 42
E-Cut saw blade, bi-metal, Fine Width of cut 30 mm	077857 30
Segmented saw blade, carbide, 1.2 mm Saw blade Ø 90 mm	077829 90
E-Cut saw blade, bi-metal, Precision Width of cut 35 mm	077850 35
Segmented saw blade, carbide, 1.2 mm Saw blade Ø 75 mm	077829 75
E-Cut saw blade, diamond, 1.2 mm	077887
Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 100 mm	077839 100
E-Cut saw blade, diamond, SLP mount Cutting width 35 mm	077849 35
Segmented saw blade, diamond, 1.2 mm Saw blade Ø 75 mm	077830 75
E-Cut saw blade, Carbide Pro Cutting width 35 mm	077893 35
Segmented saw blade, diamond, 1.2 mm Saw blade Ø 90 mm	077830 90
E-Cut saw blade, bi-metal, Universal Width of cut 44 mm	077856 44
E-Cut saw blade, standard, 5 pieces Width of cut 65 mm	077840 65
Saw blade, bi-metal HSS Saw blade Ø 85 mm	077838 85
E-Cut saw blade, standard Cutting width 65 mm	077844 65
E-Cut saw blade, bi-metal, Long-Life Cutting width 20 mm	077847 20
E-Cut saw blade set, MiniCut3 pieces Version SET	077859 SET
Segmented saw blade, diamond, 2.2 mm Saw blade Ø 75 mm	077867 75
Saw blade, bi-metal HSS, 5 pieces Saw blade Ø 85 mm	077839 85
E-Cut saw blade, standard, 5 pieces Width of cut 35 mm	077840 35
E-Cut saw blade, curved Cutting width 35 mm	077870 35
Segmented saw blade, carbide Saw blade Ø 90 mm	077828 90