



MultiMaster MM 700 Max Top Cordless, Type: 71293462



Order data

Order number	077805 71293462
GTIN	
Item class	03F

Description

Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Most suitable MultiTool for rapid work progress (for interior work and renovating) with bi-metal saw blade for wood, metal and plastics. Thanks to the StarlockMax arbor, you have access to around 180 FEIN accessories from the Starlock, StarlockPlus and StarlockMax performance classes.

Supplied with:

Supplied with 1 pc. E-Cut saw blade 44 mm and plastic tool case.

Note:

Suitable rechargeable batteries for MultiVolt battery interfaces can be found under No. 073832.

Without battery and without charger.

Technical description

Manufacturer's designation	AMM 700 Max Select
Weight	1.1 kg
Battery voltage	18 V
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Speed of oscillation	10000 - 19500 min ⁻¹
Toolholder	StarlockMax
Power supply	Rechargeable battery-powered
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Type of product	Oscillator