



## MultiMaster AMM 300 Plus Start Cordless, Type: 71293261



### Order data

Order number	077825 71293261
GTIN	
Item class	03F

### Description

#### Version:

Market-leading oscillating tools in three different performance classes (SuperCut, MultiMaster, MultiTalent) in a new version with **Starlock tool arbor** (improved torque transmission of up to 35 % greater rate of progression of the work).

- **Virtually unlimited application possibilities (sawing, grinding, scraping, cutting, rasping) due to the oscillating mode of movement (low generation of dust).**
- **Stepless electronic speed control for optimum working.**
- **Very high quality and stability thanks to the metal gearbox and use of ball bearings and needle bearings throughout.**
- **Optimum handling due to ergonomic design with soft-grip inlays and low weight.**

Thanks to the Starlock Plus tool arbor, you have access to around 100 FEIN accessories from the Starlock and Starlock Plus performance classes.

MultiTool for interior work and renovation with the basic equipment for sawing wood, metals, plasterboard and plastics.

#### Supplied with:

1 pc. plastic tool case, 1 pc. E-Cut long-life saw blade (35 mm), 1 pc. E-Cut long-life saw blade (65 mm), 1 pc. E-Cut universal saw blade (44 mm).

Incl. 1× ALG 80 quick charger, 2× Li-ion rechargeable battery packs (12 V / 3 Ah).

#### Note:

See from No. 073834 and 073845 for suitable replacement batteries and chargers.

### Technical description

Type of rechargeable battery	Lithium-ion
Battery voltage	12 V
Manufacturer's designation	AMM 300 Plus Start
Toolholder	Starlock, Starlock Plus
Speed of oscillation	11500 min <sup>-1</sup>
Number of rechargeable batteries contained	2
Weight	1.5 kg
Power supply	Battery-powered
Battery capacity	3 Ah
Amplitude (oscillation movement)	2 × 1.6 degrees
Packaging	Carrying case
suitable battery - supplier / battery type / voltage	Fein type E 12 V
Type of product	Oscillator