

Garant
SNHX 1205 left-hand, Type: UNI

Order data

Order number	218613 UNI
GTIN	4062406537944
Item class	21A

Description
Note:

Standard application values for a_e max.

To machine a flat slot base, left and right inserts must be mounted on the carrier. The side facing away from the shank is equipped with left inserts.

Technical description

Chamfer width	0.25 mm
Type	UNI
Grade	HB7835
ISO code indexable insert	SNHX 1205
Tool material	Carbide
Insert thickness	5.4 mm
for slot width a_p	10; 14 mm
Number of changes/inserts	4

Type of product

Indexable insert for milling