



Abrasive flap disc long life ZA, conical, Ø 100 mm, Grit: 120



Order data

| | |
|--------------|---------------|
| Order number | 565283 120 |
| GTIN | 4062406537975 |
| Item class | 52M |

Description

Version:

- High-quality zirconium aluminium oxide (ZA) for high abrasive performance.
- Glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on angle grinders of all power classes.

long life - very closely spaced flap strips, for **maximum tool life**. Bore Ø 16 mm.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

| | |
|----------------------|-------------------------|
| Shape description | dished |
| Bore Ø | 16 mm |
| Disc Ø | 100 mm |
| Grinding media | Zirconium abrasive (ZA) |
| Grinding medium code | ZA |

| | |
|---|--------------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 100 mm |
| optimised for material | INOX |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |