

Garant
SNHX 1103 right-hand, Type: UNI

Order data

Order number	218585 UNI
GTIN	4062406537982
Item class	21A

Description
Note:

Standard application values for a_e max.

To machine a flat slot base, left and right inserts must be mounted on the carrier. The side facing away from the shank is equipped with left inserts.

Technical description

Grade	HB7835
Type	UNI
Chamfer width	0.25 mm
ISO code indexable insert	SNHX 1103
Tool material	Carbide
Insert thickness	2.7 mm
for slot width a_p	5 mm
Number of changes/inserts	4

Type of product

Indexable insert for milling