

Garant
SNHX 1205 right-hand, Type: UNI

Order data

| | |
|--------------|---------------|
| Order number | 218615 UNI |
| GTIN | 4062406538118 |
| Item class | 21A |

Description
Note:

Standard application values for a_e max.

To machine a flat slot base, left and right inserts must be mounted on the carrier. The side facing away from the shank is equipped with left inserts.

Technical description

| | |
|---------------------------|-----------|
| Grade | HB7835 |
| Chamfer width | 0.25 mm |
| Type | UNI |
| ISO code indexable insert | SNHX 1205 |
| Tool material | Carbide |
| Insert thickness | 5.4 mm |
| for slot width a_p | 10; 14 mm |
| Number of changes/inserts | 4 |

Type of product

Indexable insert for milling