

Garant
SNHX 1207 right-hand, Type: UNI

Order data

Order number	218625 UNI
GTIN	4062406538125
Item class	21A

Description
Note:

Standard application values for a_e max.

To machine a flat slot base, left and right inserts must be mounted on the carrier. The side facing away from the shank is equipped with left inserts.

Technical description

Grade	HB7835
Chamfer width	0.25 mm
Type	UNI
ISO code indexable insert	SNHX 1207
Tool material	Carbide
Insert thickness	7 mm
for slot width a_p	12; 16 mm
Number of changes/inserts	4

Type of product

Indexable insert for milling