



Mini hacksaw for hacksaw blades – with bimetal blade 24 teeth, Type: 300



Order data

Order number	580900 300
GTIN	7311518017545
Item class	58Z

Description

Version:

Sturdy saw blade holder made of injection moulded alloy with simple blade tensioning. Overall length 330 mm.

The bow saw with its prominent bow frame is characterised by the u-shaped bow which tensions the saw blades. The limitation in depth of cut of hand bow saws is presented by the distance from the blade to the bow. This frame shape permits the use of particularly slim saw blades, which in other frame shapes would be liable to buckle when subjected to cutting movements with the force in alternate senses or other than in the pulling sense. Thanks to the thin hacksaw blades the metal cutting effort required is reduced, because of the small cutting width. Thus this type of saw is the classic standard for hacksaw work in metalworking.

Application:

For comfortable sawing including flush sawing with metal saw blades No. 582500 – 582970, in narrow, inaccessible places.

Supplied with:

Supplied with SANDFLEX® bimetal hacksaw blade.

Technical description

TPI	24
Blade length	250 mm
Type of product	Hacksaw frame

