



Climate measuring instrument CO₂ set with Bluetooth, Type: CO₂



Order data

Order number	474167 CO ₂
GTIN	4029547019401
Item class	47B

Description

Version:

Climate measuring instrument Testo 440 CO₂ set with Bluetooth **for assessing the air quality in the room**. CO₂ probe with Bluetooth incl. temperature and moisture sensor.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Climate measuring instrument No. 474141 size 440, 3 pcs. mignon batteries type AA, USB cable for CO₂ probe No. 474157 size CO₂, case No. 474158 and calibration certificate.

Calibration: Price on request

IP Index of Protection: IP 54

Measuring range: 0 – 10000

Accuracy (ppm + % of measured value): ±50 + 3 % (0 to 5000 ppm) ±100 + 5 % (0 to 10,000 ppm) ppm

Technical description

Power supply	Battery-powered
IP Index of Protection	IP 54
Number of batteries contained	3

Battery type	AA
Measuring range	0 – 10000
Accuracy (ppm + % of measured value)	$\pm 50 + 3\%$ (0 to 5000 ppm) $\pm 100 + 5\%$ (0 to 10,000 ppm) ppm
Interface	Bluetooth interface
Interface	USB interface
Device memory	7500 measurement reports
Calibration	Price on request
Type of product	Climate measuring instrument