



POLIFFAN-STRONG (ZA) abrasive flap disc for steel, 125 mm Ø, Grit: 40



Order data

Order number	566322 40
GTIN	4007220777886
Item class	55P

Description

Version:

Abrasive flap disc for demanding machining.

The patented design with **high coating density** for **high removal rate** and **tool life**.

Technical description

Shape description	dished
Bore Ø	22.23 mm
Disc Ø	125 mm
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	125 mm Ø
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	Suitable		
Steel < 1400 N/mm ²	Suitable		
Steel < 55 HRC	Suitable		
Steel < 60 HRC	Suitable		
Steel < 67 HRC	Suitable		
INOX	Suitable only under restricted conditions		
Ti	Suitable only under restricted conditions		
GG(G)	Suitable only under restricted conditions		
dry	Suitable		