

HEDI

LED cordless rod lamp, Type: 160



Order data

Order number	081259 160
GTIN	4003644006090
Item class	08B

Description

Version:

Battery-powered rod lamp with rotating plastic hook; On/Off switch, floodlight and torch can be controlled separately.

Bright floodlight via 160 LEDs. With 230 V / 12 V charger and in-car charging cable.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

IP Index of Protection: IP 20

ATEX zone: no

Illumination: 400 lm

Working life: 3 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Nickel metal hydride

Overall length: 520 mm

Technical description

ATEX zone	no
Weight	300 g
Power supply	Rechargeable battery-powered
Illumination	400 lm
Type of rechargeable battery	Nickel metal hydride
IP Index of Protection	IP 20
Number of rechargeable batteries contained	1

Overall length	520 mm
Working life	3 h
Head Ø	58 mm
Type of product	Inspection lamp