



2-component adhesive, Manufacturer ID: DP190



Order data

Order number	083374 DP190
GTIN	4054596677234
Item class	08M

Description

Version:

Tough resilient 2-component adhesive for quick and easy jointing, makes a permanent joint. Cures at room temperature.

Application:

Use manual application gun No. 083373 size PISTOLE together with delivery piston No. 083375 size KOLBEN3 and mixing tubes No. 083383 size MIXER.

Technical description

Manufacturer's designation	DP190
Tensile shear strength	18 N/mm ²
Density	1.3 g/cm ³
Processing temperature	20 - 25 °C
Dynamic viscosity	60000 mPas
Touch dry after	480 min

Functional strength to	360 min
Shape	liquid
Colour	grey
Suitable for material	Metal
Suitable for material	wood
Suitable for material	Plastic
Storage temperature	15 - 25 °C
Working life after date of manufacture	15 mo
Hardness according to Shore A	35
UN number	UN3082
Chemical basis	Epoxy resin
Capacity	50 g
hazardous goods class	9
Operating temperature range	-55 - 80 °C
Resistant to impacts and vibrations	no
Lap shear strength	17.6 N/mm ²
Type of product	Two-component adhesive