

Garant

**Shrink-fit chuck vibration-damped, with cooling channel bores, SK 40 A = 160,
Clamping range Ø D1: 16mm**



Order data

Order number	302210 16
GTIN	4062406545529
Item class	31A

Description

Version:

- **High-temperature steel.**
- **Integrated length adjustment of the tools.**
- **For HSS and solid carbide tools.**
- **Shanks hard turned (smooth cutting action!).**
- **With RFID / Balluffchip bore.**
- **With coolant channel bores and threads that can be sealed.**
- **With tapped holes on each side for balancing screws.**
- **Reinforced version/contour.**
- **Polished surface.**
- **Specially mounted carbide core in the shrink-fit chuck body.**

Advantage:

- **Vibration-damping.**
- **Better workpiece surface finish.**
- **Optimised tool life.**
- **Increased process reliability.**
- **Lower corrosion tendency due to polished surface.**

Application:

For clamping tools with plain shank (h6 shank tolerance). Suitable for inductive, contact and hot air shrink-fit units.

Optional extras:

Pull studs (PS) No. 308600 – 308800.

PS wrenches No. 308820 – 308835.

Shrink-fit chuck extensions No. 302410 – 302419.

Shrink-fit units, accessories No. 354210 – 354450.

Balancing screws set No. 309906 size 180.

Technical description

Ø D ₂	27 mm
Overhang dimension A	160 mm
Cooling channel bore	pluggable
Clamping Ø D ₁	16 mm
External Ø D	34 mm
Ø D ₃	50 mm
L ₂	85.9 mm
Adapter	SK 40 A = 160
Arbor standard	ISO 7388-1
Shape	ADB
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Vibration	damped
Type of product	Shrink-fit chuck