

Garant**Adapter $\varnothing d = 32$ mm, Shank $\varnothing D_s$: 12mm**

Order data

Order number	293105 12
GTIN	4062406560942
Item class	29K

Description

Application:

With this adapter, cutter inserts for outer profiles can also be used in conjunction with a profile broaching holder for inner profiles.

Suitable for:

Profile broaching holder for internal profiles No. 293023, 293030, 293073.

Note:

For reasons of stability, use the profile broaching holder No. 293102 on higher batch sizes or materials that are difficult to machine.

Technical description

Shank $\varnothing D_s$	12 mm
$\varnothing d$	32 mm
Profile length t_{max}	20 mm
L	17 mm
Shank length L_s	15 mm

Head length L ₁	25.5 mm
Type of product	Keyway broaching and profile slotting tool