

Garant**Profile broaching insert for external hexagon $\varnothing d = 32$ mm, TiN, Hexagon: 4mm****Order data**

Order number	293110 4
GTIN	4062406560973
Item class	29L

Description**Version:**

With TiN coating.

Note:

Special geometries on request. Detailed application values can be found in our application ToolScout.

Technical description

L_1	20.5 mm
$\varnothing d$	32 mm
Hexagon	4 mm
Profile	Hexagon
Tool material	HSS
Profile length t_{max}	40 mm

Tolerance	- 0.06 to - 0.1 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool