

Garant**Profile broaching holder $\varnothing d = 32$ mm, Shank $\varnothing DS: 32$ mm****Order data**

Order number	293102 32
GTIN	4062406560935
Item class	29K

Description**Suitable for:**

CNC and conventional machines.

Technical description

L	41.5 mm
Shank type	Plain shank
Shank length L_s	50 mm
Shank $\varnothing D_s$	32 mm
$\varnothing D$	44 mm
$\varnothing d$	32 mm
Head length L_1	50 mm
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool

