



Pipework linisher, Type: 72216660



Order data

Order number	077715 72216660
GTIN	
Item class	03F

Description

Version:

Pipework linisher with **extremely high stock removal rate**. Ideal for **working on pipes and pipe elbows**, cleaning up, removal of colouration, grinding weld seams, preparation for polishing, and polishing to mirror finish. Speed range variable for grinding, linishing, and polishing belts. **Improved belt guidance**. For stainless steel pipes, pipe diameter 8–45 mm.

Supplied with:

1 pipework linisher RS 10-70 E, 10 each linishing belts K120/K180, 5 pieces fine fleece belts, plastic tool case.

Note:

Linishing belts can be found from No. 558011.

Technical description

Type	72216660
Power supply	Battery-powered
Band length	533 mm
Manufacturer's designation	RS 10-70 E
maximum vibration to EN	4.5 m/s ²
pipework Ø for linishing	8 - 45 mm

maximum belt speed	350 - 1100 mm/s
Power consumption	800 W
Tape width	30 mm
Weight	2.9 kg
Type of product	Pipework finishers

Accessories

Aluminium Oxide (A) finishing beltKK711T Grit 60	558011 60
Aluminium Oxide (A) finishing beltKK711T Grit 120	558011 120
Aluminium Oxide (A) finishing beltKK711T Grit 80	558011 80
Aluminium Oxide (A) finishing beltKK711T Grit 180	558011 180
Aluminium Oxide (A) finishing beltKK711T Grit 40	558011 40