



Combination spanner set, Number of keys: 11



Order data

Order number	613810 11
GTIN	4013288214195
Item class	63F

Description

Version:

Particularly suitable where space is tight. The combination of the 7.5° offset for the open jaws and the bi-hexagon geometry for the ring achieves a doubling of the application points. The small working arc of the open jaws allows the bolt head to be gripped every 15° of rotation. Drop-forged. With close tolerance jaw width.

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome molybdenum steel, matt chrome-plated.

Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970:
Size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 613610

Technical description

Width across flats	metric
--------------------	--------

Number of keys	11
Manufacturer's designation	6003 Joker 11 set 1
Ring setting	15 degrees
Material	Chromium-molybdenum steel.
Surface	matt chrome-plated
Measurement system metric	yes
Measurement system imperial	no
Long version	no
Type of product	Spanner

Accessories

Combination spanner Width across flats 13 mm	613800 13
Combination spanner Width across flats 14 mm	613800 14
Combination spanner Width across flats 15 mm	613800 15
Combination spanner Width across flats 17 mm	613800 17
Combination spanner Width across flats 19 mm	613800 19
Combination spanner Width across flats 11 mm	613800 11
Combination spanner Width across flats 10 mm	613800 10
Combination spanner Width across flats 16 mm	613800 16
Combination spanner Width across flats 18 mm	613800 18
Combination spanner Width across flats 8 mm	613800 8
Combination spanner Width across flats 12 mm	613800 12