

Garant GRIDLINE

Base cabinet with divider with Viewing window swing doors, Type: 2000-3



Order data

Order number	940084 2000-3
GTIN	4062406565114
Item class	9GI

Description

Version:

Equipped cabinet in 40x20G with divider. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. Centre partition throughout, all storage shelves height-adjustable.

Fitted with:

Number of shelves width 20G: 5

Supplied with:

Cabinet with divider and storage shelves.

Colour:

Body RAL 7035 light grey, **powder-coated**.

Doors RAL 7016 anthracite, **powder coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Data sheet

Width	1000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
ComfortClose	no
Cabinet fronts	Viewing window swing door
Electronic locking system can be retrofitted	yes
Handle positioning	centre
Weight	142 kg
Depth	500 mm
Width in G	40
Depth in G	20
Usable height	1845 mm
Height	2000 mm
Hoffmann perforated panel grid interval	9×9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Storage shelf for cabinet / compartment width in G 20	940550 20