

Garant GRIDLINE

**Base cabinet with divider and drawers with plain sheet metal swing doors,
Type: 2000-1****Order data**

| | |
|--------------|---------------|
| Order number | 940102 2000-1 |
| GTIN | 4062406545208 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 40x20G with centre partition and drawers, depth 16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. Drawers with front height 125 mm. Suspended centre partition with one fixed and 2 height-adjustable storage shelves. Load capacity of the suspended centre partition or suspended compartment: 200 kg.

Fitted with:

Number of shelves width 20G: 3

Number of shelves width 40G: 1

Number of drawers 16×16G: 1

Number of drawers 36×16G: 2

Supplied with:

Cabinet with divider, storage shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|---|------------------------------|
| Drawer usable depth | 400 mm |
| Usable height | 1845 mm |
| Handle positioning | centre |
| Drawer/pull-out shelf load capacity | 75 kg |
| Weight | 145 kg |
| Cabinet fronts | Plain sheet metal swing door |
| Electronic locking system can be retrofitted | yes |
| Drawer usable width | 400 mm |
| Drawer usable width | 900 mm |
| Drawer usable depth in G | 16 |
| ComfortClose | no |
| Width | 1000 mm |
| Depth in G | 20 |
| Width in G | 40 |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Height | 2000 mm |
| Depth | 500 mm |
| Drawer usable width in G | 16 |
| Drawer usable width in G | 36 |
| Hoffmann perforated panel grid interval | 9×9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |

| | |
|------------------|--|
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Type of product | Cabinet with shelves |

Accessories

| | |
|---|-------------|
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm | 940640 125 |
| Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm | 940642 125 |
| Storage shelf for cabinet / compartment width in G 20 | 940550 20 |
| Storage shelf for cabinet / compartment width in G 40 | 940550 40 |