

Garant GRIDLINE

**Base cabinet with divider and drawers with plain sheet metal swing doors,
Type: 2000-2****Order data**

Order number	940102 2000-2
GTIN	4062406565213
Item class	9GI

Description**Version:**

Equipped cabinet in 40x20G with centre partition and drawers, depth 16G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. Drawers with front height 125 mm. Suspended centre partition with 2 fixed and 4 height-adjustable storage shelves. Load capacity of the suspended centre partition or suspended compartment: 200 kg.

Fitted with:

Number of shelves width 20G: 6

Number of shelves width 40G: 1

Number of drawers 16×16G: 2

Number of drawers 36×16G: 1

Supplied with:

Cabinet with divider, storage shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Plain sheet metal swing door
Drawer usable depth	400 mm
Drawer usable width in G	16
Drawer usable width in G	36
Handle positioning	centre
Drawer usable depth in G	16
ComfortClose	no
Width	1000 mm
Depth in G	20
Depth	500 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Height	2000 mm
Drawer/pull-out shelf load capacity	75 kg
Usable height	1845 mm
Weight	142 kg
Electronic locking system can be retrofitted	yes
Drawer runner extension (partial/full extension)	100 %
Width in G	40
Hoffmann perforated panel grid interval	9×9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Storage shelf for cabinet / compartment width in G 20	940550 20
Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125
Storage shelf for cabinet / compartment width in G 40	940550 40
Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm	940642 125