

# uvex

## Sandal, black/yellow uvex 1, S1, EU shoe size: 39



### Order data

Order number	092110 39
GTIN	4031101543055
Item class	04V

### Description

#### Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Safety sandals with double hook and loop fastening and large ventilation openings.

#### Standard:

EN ISO 20345:2011 S1 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S1

Material of protective toe-cap: Composite

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

EU shoe size	39
against water penetration and water absorption	no

Standard	Inlay type-tested according to DGUV regulation 191
suitable for those with chrome allergy.	yes
Material of outer sole	PU
The entire shoe is waterproof	no
Size UK	5.5
oil- and petrol-resistant sole	no
Shoe type	Sandals
Energy absorption in the heel area	yes
Colour	black / yellow
Slip resistance	yes
Material inner lining	Distance Mesh lining material
removable footbed	yes
profiled outer sole	yes
Material of protective toe-cap	Composite
Size US	7.5
Uppers material	Hydrophobic high-tech micro-velour
Closure	Hook and loop fastener
Protection class	S1
anti-static	yes
Series	uvex 1
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety sandals