

HEDI

Machine lamp, Type: 9LED-24V



Order data

Order number	081303 9LED-24V
GTIN	4003644016709
Item class	08B

Description

Version:

High-quality, universally usable lamps, with On/Off switch, 3 m rubber connection cable. Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability.

All Hedi® machine/workstation lights come as standard with table clamps, integrated magnet and 4 screws for flexible attachment of the lamp to a variety of surfaces.

Proven machine lamp with extremely sturdy lamp head, protected against splashed water and dust-tight, for professional use in tough working environments or use on and in machines. Radio interference suppression according to DIN EN 62493.

Function:

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

IP Index of Protection: IP 64

Nominal voltage: 24 V

Light focussing: focussed tight beam

Beam dispersion angle fixed: 60 °

Light output: 12 W

Illumination: 1140 lm

Technical description

Nominal voltage	24 V
Power supply	Mains operated
Illumination	1140 lm
Light output	12 W
ATEX zone	no
IP Index of Protection	IP 64
Beam dispersion angle fixed	60 °
Light focussing	focussed tight beam
Type of product	Machine lamp