

HEDI

Machine lamp, Type: 6LED



Order data

Order number	081301 6LED
GTIN	4003644000111
Item class	08B

Description

Version:

High-quality, universally usable lamps, with on/off switch, 3-m rubber connection cable. All HEDI® machine/workstation lamps come with table clamps, integrated magnet and 4 screws for flexible attachment of the lamp to a wide variety of surfaces as standard. Classic machine lamp in wide-beam version. Lamp head can be rotated and swivelled 340° using the ball joint. With exchangeable light source.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Technical description

Light output	7 W
ATEX zone	no
Light colour	cold white
Power supply	Mains operated
IP Index of Protection	IP 20

Power consumption	7 W
Colour temperature	6500 K
Illumination	621 lm
Bulb	LED
Type of product	Machine lamp