

# HEDI

## Machine lamp, Type: 3LED



### Order data

Order number	081301 3LED
GTIN	4003644014941
Item class	08B

### Description

**Version:**

High-quality, universally usable lamps, with on/off switch, 3-m rubber connection cable.

All HEDI® machine/workstation lamps come with table clamps, integrated magnet and 4 screws for flexible attachment of the lamp to a wide variety of surfaces as standard.

Classic machine lamp in wide-beam version. Lamp head can be rotated and swivelled 340° using the ball joint. With exchangeable light source.

**Function:**

IP20: No protection against penetration by foreign bodies with  $\varnothing < 12$  mm, however touching should be avoided, and no protection against water.

### Technical description

Illumination	480 lm
Light colour	cold white
Bulb	LED
Light output	5.5 W
ATEX zone	no

Colour temperature	6500 K
Power consumption	5.5 W
Power supply	Mains operated
IP Index of Protection	IP 20
Type of product	Machine lamp