

Kroeplin
Längenmesstechnik

Digital external quick caliper with spherical anvils, Measuring range: 0-30mm



Order data

Order number	438573 0-30
GTIN	2050002053168
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 2 batteries No. 081561 size LR3.

Optional extras:

Data cable adapter No. 498954 size A2, data cable No. 497440 and radio adapter No. 498954 size A5.

Technical description

Measurement tip length top Hb	30 mm
Gauging force	1 - 1.5 N
Measurement tip length bottom Hf	30 mm
maximum contact point length L (measurement depth)	115 mm
Repetition accuracy	0.02 mm
Measuring range	0 - 30 mm

Number of batteries contained	2
Power supply	Battery-powered
IP Index of Protection	IP 67
Error limit	0.04 mm
Article no of the battery / rechargeable battery fitted	081561 LR3
Carbide spherical point \varnothing	3 mm
Graduations can be switched over	0.001 mm
Graduations can be switched over	0.002 mm
Graduations can be switched over	0.005 mm
Graduations can be switched over	0.01 mm
Graduations can be switched over	0.02 mm
Graduations can be switched over	0.05 mm
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Interface	Bluetooth interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	External quick callipers

Services

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S