

**Cordless hand-held circular saw, Type: GKS18V68C****Order data**

Order number	078183 GKS18V68C
GTIN	3165140931786
Item class	03B

**Description****Version:**

Powerful 18 V **cordless circular saw with BITURBO technology.**

- **Integrated VAC adaptor for easy manoeuvring. Adaptor can be rotated 360°.**
- **Best possible ergonomics for maximum control and comfort.**
- **Intelligent brake for safe stopping with minimised kick-back.**
- **Equipped with professional 18 V system for light to heavy-duty applications.**

**Supplied with:**

Including saw blade, parallel guide.

**Note:**

Circular saw blades can be found under 583920.

See from No. 073851 and No. 073866 for suitable spare batteries and chargers.

**Technical description**

Battery voltage	18 V
Weight	4.7 kg
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Saw blade bore Ø	30 mm
Type of rechargeable battery	Lithium-ion

Packaging	Modular case (L-Boxx)
Weight without battery	3.8 kg
maximum speed	6250 min <sup>-1</sup>
Power supply	Rechargeable battery-powered
Saw blade Ø	190 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum cutting depth 90°	57 mm
Number of rechargeable batteries contained	0
Manufacturer's designation	GKS 18V-68 C
Version	Plunging circular saw
Type of product	Saw

## Accessories

Li-ion battery Battery type, battery voltage B18 V	073851 B18
Circular saw bladeexpert for Aluminium Blade Ø D 190 mm	583920 190
Li-ion battery Battery type, battery voltage B18 V	073854 B18
Battery charger Type GAL18160C	073866 GAL18160C
Battery charger Type GAL18V6-80	073866 GAL18V6-80
Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B18 V	073853 B18
Circular saw blade, metal, alternating teeth with beveluniversal Blade Ø D 190 mm	584095 190
Circular saw blade, wood, alternating teethuniversal Blade Ø D 190 mm	584075 190