

 steinel
18V cordless heat gun, Type: 063993



Order data

Order number	078323 063993
GTIN	4007841063993
Item class	07E

Description

Version:

Compact cordless heat gun mobile heat MH 5 offers four application-specific programs. Air volume can be regulated digitally in six steps (up to 300 l/min).

Supplied with:

Version without battery and without charger, case.

Note:

See No. 073870 – No. 073890 for suitable batteries and chargers.

Technical description

Battery voltage	18 V
Power consumption	2200 W
Packaging	Carrying case
Air temperature	50 - 500 °C
Air flow volume	300 l/min
Number of rechargeable batteries contained	0

Power supply	Rechargeable battery-powered
Manufacturer's designation	MH5
Weight	660 g
suitable battery - supplier / battery type / voltage	Type CAS 18 V
Type of product	Hot air pistol

Accessories

Battery charger Type ASC55	078328 ASC55
Battery Type CAS-8	078327 CAS-8
Battery charger Type ASC145	078328 ASC145