



LED cordless lamp 0 version without battery, 18 V, Type: M18HOSALC



Order data

Order number	073211 M18HOSALC
GTIN	4058546340490
Item class	07A

Description

Version:

Robust Li-Ion battery lights with high light intensity.

- **Very sturdy 18 Volt LED floodlight with stand.**
- **Shock-resistant radiator head with 3 separate and individually adjustable LED modules.**
- **Hybrid power source: operates either with an 18V rechargeable battery or with a cable.**
- **Integral M18™ rechargeable battery charger and 2.1 ampere USB charger.**

Function:

IP34: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 2.5$ mm, however tools and wires should be kept away.

Suitable for:

Milwaukee 18 V batteries (No. 073816 MB18 and 073827 MB18).

Supplied with:

Cordless lamp without battery and without charger.

Technical description

IP Index of Protection	IP 34
ATEX zone	no

Power supply	Rechargeable battery-powered
Illumination step 2	4000 lm
Illumination time stage 2	5 h
Weight including rechargeable battery	11100 g
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Bulb	LED lamp
Battery voltage	18 V
Illumination	6000 lm
Illumination time stage 3	10 h
Manufacturer's designation	M18 HOSALC-0
Illumination step 3	1700 lm
Product name attribute	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Work lamp