



Telescopic single ladder, Number of steps: 9



Order data

Order number	966096 9
GTIN	4031405407626
Item class	96Y

Description

Version:

Telescopic ladder of aluminium with stable triangular hollow section stiles, abrasion-resistant anodised. 80-mm deep, corrugated **steps** and 2 bottom steps (50 mm). High-strength step/stile connection. Step spacing / rung spacing 300 mm. Maximum load capacity 150 kg. Intuitive telescopic function for easy height adjustment. When closed up, the ladder fits in a car boot.

Standard:

DIN EN 131.

Technical description

Weight	10.2 kg
Number of steps	9
Material	Aluminium
Width	470 mm
Rung/step depth	85 mm
Type of step	step

Ladder length extended	3 m
Ladder length closed	0.76 m
Working height approx.	3.8 m
Ladders and platforms load capacity	150 kg
Type of product	Lean-to ladder