



GÜNZBURGER STEIGTECHNIK

## Telescopic single ladder, Number of steps: 13



### Order data

Order number	966096 13
GTIN	4031405407619
Item class	96Y

### Description

#### Version:

Telescopic ladder of aluminium with stable triangular hollow section stiles, abrasion-resistant anodised. 80-mm deep, corrugated **steps** and 2 bottom steps (50 mm). High-strength step/stile connection. Step spacing / rung spacing 300 mm. Maximum load capacity 150 kg. Intuitive telescopic function for easy height adjustment. When closed up, the ladder fits in a car boot. Including fold-away cross beam (supplied loose).

#### Standard:

**DIN EN 131.**

### Technical description

Material	Aluminium
Rung/step depth	85 mm
Ladder length extended	4.1 m
Cross-span width	0.89 m
Working height approx.	4.9 m

Number of steps	13
Ladder length closed	0.93 m
Weight	17.6 kg
Width	565 mm
Type of step	step
Ladders and platforms load capacity	150 kg
Type of product	Lean-to ladder