

**Velour-backed abrasive disc (CER) Hookit 775L No holes, Ø 150 mm, Grit: 80****Order data**

Order number	567793 80
GTIN	50051125868209
Item class	53M

**Description****Version:**

With **stable film backing**. Dust-repellent coating prevents premature clogging.

**Advantage:**

- **More uniform surface finish due to outstanding grit support.**
- **Improved tear resistance when the edges are stressed.**

**Application:**

High-quality aluminium oxide abrasive grit (A) for general coarse, intermediate and finishing use.

**Cubitron™ II** precision grit with the advantage of **quicker material removal** and **more consistent surface finish** on large areas (sheet metal work).

**Technical description**

Disc Ø	150 mm
Series	775L
Grit	80
Grinding media	Cubitron™ II

Grinding medium code	Stainless steel
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 150 mm
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		