

3M**Velour-backed abrasive disc 237AA (A), Ø 115 mm, Grit: 280****Order data**

Order number	567724 280
GTIN	2050002053328
Item class	51E

Description**Version:**

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

237AA Trizact™ with fine-structured pyramidal surface of micro-Aluminium Oxide mineral particles (A).

Application:

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

For a **fine and uniform surface finish** all steels, stainless steels, brass and titanium alloys. Specially for contour grinding and preparation for polishing.

Note:

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

Technical description

Grit	280
------	-----

Disc Ø	115 mm
Series	237AA
3M grit designation	A65
Manufacturer's designation	237AA Trizact™
Grinding media	Aluminium oxide mineral particles (A)
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Propulsive equipment	Angle grinder
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
dry	suitable		