



Cordless sabre saw, Type: M18ONEFSZ



Order data

Order number	078220 M18ONEFSZ
GTIN	4058546344733
Item class	03L

Description

Version:

Milwaukee cordless sabre saw for working in difficult-to-access areas.

- **Electronic controls with steplessly variable stroke length and overload protection.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**

Cordless sabre saw.

- **New generation of the brushless POWERSTATE™ motor for greater efficiency.**
- **Patented clutch protection prevents the tool jerking when the saw blade jams.**
- **Controllable soft start for maximum speed and control.**
- **Tool-less FIXTEC saw blade quick-release clamping system.**
- **Tiltable and adjustable saw base plate, permits optimisation of the cutting position.**

Version M18FSZ but with **ONE-KEY™** technology.

- **Up to 3 individual profiles can be saved on the internal memory of the device.**

Supplied with:

Variant in HD box **without battery, without charger.**

Note:

Sabre saw blades can be found from No. 588600.

See No. 073810; 073811; 073814; 073815; 073816; 073829 for suitable spare batteries and chargers.

Technical description

maximum vibration to EN	9.9 m/s ²
Stroke length	32 mm
Battery voltage	18 V
App link	OneKey
Packaging	Modular case (HD=Heavy Duty)
Weight	7.9 kg
Power supply	Rechargeable battery-powered
Rate of strokes	0 - 3000 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Battery capacity	5 Ah
Number of rechargeable batteries contained	0
Special features	FIXTEC, LED
Manufacturer's designation	M18 ONE FSZ
Type of rechargeable battery	Lithium-ion
Type of product	Saw

Accessories

Battery starter setHigh Output™ Type M18HNRG55	073830 M18HNRG55
Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Li-ion system M18B5 Battery type MB18	073816 MB18
Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Battery starter set Type M18NRG5	073839 M18NRG5
Battery starter setHigh Output™ Battery type M18HNRG3	073826 M18HNRG3
Li-ion batteryHigh Output™ Battery type MHB3	073808 MHB3
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8
Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8

Li-ion system M18B2 Battery type MB18	073827 MB18
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12