

Ansell**Pair of gloves HyFlex® 11-819 ESD, Glove size: 9****Order data**

Order number	094354 9
GTIN	10076490614048
Item class	04P

Description**Version:**

HyFlex® 11-819 ESD. Perfect combination of wearing comfort, freedom of movement for the fingers and ESD/touch screen compatibility. Protective product against electrostatic discharge. As part of the earthing chain, it can also be worn in potentially explosive areas. Dermatologically tested with Dermatest®, Oeko-Tex certified.

Standard:

EN 16350

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

Technical description

Glove size	9
Protection category	Category II

Type of glove	Multi-purpose gloves
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Suitable for touch screens
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	free of latex
Glove characteristics	Silicone-free
electrostatic characteristic	EGB/ESD
EN 388	3121A
Backing material	Nylon Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	Precision
Length	195 mm
Colour	blue
Weight	16.6 g
Knitted technology	18G
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves