

**Battery / mains radio, Type: M12RCDAB****Order data**

Order number	073960 M12RCDAB
GTIN	4058546325107
Item class	03L

**Description****Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation. Battery/mains radio with charging function. DAB+, AM and FM tuner.

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

**Technical description**

Number of rechargeable batteries contained	0
Frequency range	Radio frequency FM
Frequency range	Radio frequency AM
Frequency range	Radio frequency DAB
Height	386 mm

Width	155 mm
Length	523 mm
Power supply	Battery-powered
Power supply	Rechargeable battery-powered
Weight	1.9 kg
Manufacturer's designation	M12RCDAB+-0
Battery voltage	12 V
IP Index of Protection	IP 54
Interface	Digimatic interface
Interface	Bluetooth interface
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of product	Radio

---

## Accessories

Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218C	073840 M1218C