



Cordless drill / driver, Type: GSR1828



Order data

Order number	070243 GSR1828
GTIN	4059952559742
Item class	03B

Description

Version:

Cordless drill/driver

- **Compact, powerful cordless drill with forward/reverse operation.**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Outstanding available and comfortable handling due to **compact design. Motor brake** for precise working.

Supplied with:

Supplied with 3x 18 V / 3 Ah Li-ion battery, charger and L-Boxx.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Packaging: Modular case (L-Boxx)

Manufacturer's designation: GSR 18V-28

Number of rechargeable batteries contained: 3

Type of rechargeable battery: Lithium-ion

Battery voltage: 18 V

maximum torque soft: 28 N·m
maximum torque hard: 63 N·m

Technical description

Quick-clamping chuck range	13 mm
Manufacturer's designation	GSR 18V-28
Packaging	Modular case (L-Boxx)
Battery voltage	18 V
Number of rechargeable batteries contained	3
maximum torque soft	28 N·m
maximum twist drill size Ø in wood	38 mm
Type of rechargeable battery	Lithium-ion
maximum twist drill size Ø in steel	8 mm
Speed range 2nd speed	0 - 1900 min ⁻¹
Speed range 1st speed	0 - 500 min ⁻¹
Power supply	Rechargeable battery-powered
maximum torque hard	63 N·m
Weight	1.1 kg
Type of product	Drill/driver

Accessories

Battery charger Type 1880CV	073866 1880CV
Li-ion battery Battery type, battery voltage B12 V	073855 B12