



Rotary hammer+ drill/driver, cordless tool set, Type: GSR-GBH



Order data

Order number	P07838 GSR-GBH
GTIN	4059952569260
Item class	03B

Description

Version:

Set consisting of the Professional Tools cordless rotary hammerGBH 18V-21 and the cordless drill/driver GSR 18V-28. Cordless hammer drill GBH 18V-21:

- **higher performance thanks to lower weight and higher impact energy.**
- **The "brushless technology" results in lower energy consumption. This leads to a 20% longer battery life compared to the predecessor model.**
- **Three different operating modes – including for light-duty chiselling work.**

Technical data:

- **Max. impact energy: 2.0 J**
- **Impact rate: 0 - 5100 rpm**
- **No-load speed: 0 - 1800 rpm**
- **Bore Ø wood / concrete: 30 / 21 mm**

Cordless drill/driver GSR 18V-28:

- **Comfortable to use thanks to the compact design.**

Technical data:

- **No-load speed: 0 - 500/0 - 1900 rpm**
- **Max. torque (soft/hard): 28/63 Nm**
- **Max. screw Ø: 8 mm**
- **Bore Ø wood/steel: 38/13 mm**

Supplied with:

1× cordless drill/driver GSR 18V-28, 1× cordless hammer drill GBH 18V-21, 2× battery GBA 4.0 Ah, 1× quick charger GAL 18V-40, 2× L-BOXX.

Technical description

Battery voltage	18 V
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Hammer drill