

RUNPOTEC
HFR KABELZIEHSPEZIALIST

Multi-function camera RC2, Probe length: 30m



Order data

Order number	814878 30
GTIN	9120045475562
Item class	86A

Description

Version:

Multi-function camera for visual inspection of places that are difficult to access. Compatible with all RUNPOTEC products with RTG Ø 6 mm, such as PowerRex (No. 814868), Runposticks (No. 814877), Runpo1 (No. 814865) and fibreglass rod (No. 814882).

- **3.5 inch TFT LCD colour display; focussing distance 30 mm – 80 mm.**
- **Camera head with 345000 pixels (640×480); image angle 64°.**
- **6 pcs. LED incorporated in the camera head.**
- **Protection class IP 67 (camera head and cable).**
- **230V or battery operation.**

Application:

Ideal for empty conduits (from internal Ø 14 mm), suspended ceilings, ducts and underfloor channels, maintenance and plant inspections.

Supplied with:

1 Runpocam RC2 with **cable (30 m)** incl. reel in carrying case, 1 each of 2-port USB charging plug 230 V and 12 V (car), 1 USB cable 3 m, 1 cordless LED high-performance lamp 320 lumens incl. charger cable, 1 micro-memory card 8 GB, 1 Runpoglider with front thread, 1 system slide, 1 magnetic fishing set, 1 connection thread set RTG Ø 6 mm, 1 fishing hook, 1 flexible attachment 12 cm, 1 thread attachment RC2.

Technical description

Camera resolution	640×480 px
Power supply	Battery-powered
Power supply	Rechargeable battery-powered
Image aperture angle	64 degrees
Probe length	30000 mm
Display size	3.5 in
Series	RC2
Display	LCD
Probe Ø	13 mm
Type of product	Endoscope