



Pipework linisher, Type: 722275



Order data

Order number	077715 722275
GTIN	4014586895871
Item class	03F

Description

Version:

Pipework linisher with high cutting speed and **extremely high removal rate**. Ideal for **working on pipes and pipe elbows**, cleaning up, removal of colouration, grinding weld seams, preparation for polishing, and polishing to mirror finish. Speed range variable for grinding, finishing, and polishing belts. **improved belt guidance**. For stainless steel pipes, pipe diameter 8-80 mm.

Supplied with:

Linishing belts 2×10 pieces 20×815 mm P120/P180, 2× 10 pieces 40×815 mm P120/P180, 5 pieces fleece belts 20×820 mm very fine, plastic tool case.

Note:

Linishing belts can be found from No. 558011.

Packaging: Carrying case

Manufacturer's designation: RS 17-70 E

Power consumption: 1700 W

Tape width: 20; 40 mm

Band length: 815 mm

pipework Ø for finishing: 8 - 80 mm

Weight: 4.2 kg

Technical description

maximum belt speed	22 mm/s
--------------------	---------

maximum vibration to EN	4.1 m/s ²
pipework Ø for linishing	8 - 80 mm
Band length	815 mm
Weight	4.2 kg
Tape width	20; 40 mm
Power supply	Battery-powered
Power consumption	1700 W
Manufacturer's designation	RS 17-70 E
Packaging	Carrying case
Type of product	Pipework linishers