



Front grip pliers chemically blacked, with grips, overall length: 200mm



Order data

Order number	705992 200
GTIN	4003773087250
Item class	73F

Description

Version:

Special, extra slim head shape for use in tight spaces. **Box joint** (= double guidance). Designed to prevent fingers being trapped. Fine adjustment at intervals by means of a spring-loaded pushbutton, can be adjusted in 5 steps to precisely adapt the width. Front gripper and side gripper function. Jaws chemically greyed, polished head, teeth additionally induction hardened (approx. 61 HRC).

Handles with multi-component coverings.

Application:

Reliable frontal gripping of even flat workpieces due to three-point system. Gripping, tightening and releasing of even hardened screw heads as well as worn bolts and screws.

Material:

Chrome vanadium electro-steel, drop forged.

Technical description

overall length	200 mm
Self-locking	yes
Number of fine adjustment steps	5
Jaw length	27 mm
Jaw capacity for pipes	7/8 in
Protection against trapping fingers	yes
Hexagon across flats	22 mm

Jaw width	11 mm
Manufacturer's designation	TwinGrip
Type of jaws	3-point system
Handle	Multi-component covering
Material	Chrome vanadium electro-steel
Type of product	Pipe pliers