



## Heavy-duty side cutter, chrome-plated Insulated to VDE, with securing eye, overall length: 200mm



### Order data

Order number	706051 200
GTIN	4003773081494
Item class	73F

### Description

#### Version:

Pliers with a securing eye for fitting a safety harness. Securing eye, welded to the grip, dynamic load capacity up to 3 m drop height.

**Insulated to DIN EN IEC 60900 / VDE 06082-201** for working at voltages up to 1000 V.

#### Application:

For use in building construction, underground construction, building maintenance, on industrial structural work, roofing work, in exhibition stand construction, etc.

#### Material:

Chrome vanadium electro-steel, drop forged.

#### Note:

Other versions and sizes available on request.

### Technical description

Cutting capacity hard wire up to Ø	3 mm
Cutting capacity piano wire up to Ø	2.5 mm
overall length	200 mm
Cutting capacity soft wire up to Ø	4.2 mm
Material	Chrome vanadium electro-steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	yes

with selectable return spring	no
with return spring	no
Type of product	Cutting pliers