

**Pair of gloves, Glove size: 12****Order data**

Order number	094300 12
GTIN	4062406569785
Item class	02H

**Description****Version:**

Breathable assembly glove with innovative, water-based PU-nitrile coating for the highest level of precision, flexibility and dexterity in dry and slightly oily working environments. Particularly finely structured surface due to intensive finishing process. Long life through very high abrasion resistance. DMF-free.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	12

Glove characteristics	DMF-free
Glove characteristics	Suitable for allergy sufferers
EN 388	4131X
Backing material	Lycra®, polyamide
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Length	255 mm
Colour	black / grey
Knitted technology	15G
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Application	reusable
Type of product	Multi-purpose gloves